

Sp O₂ Finger Probe Details

Model	Compatible manufacturer	Length M (ft)	Connector type	Model	Notes Document Name VM3/COP/.....	Probe details (colours)			Labels	
						Pad support	Button	Pads	CE	Db
854RA	Medlab/Comdek	3 (10)	Redel M-7	854RA	VM3/COP/32.01	White	White	White	White	Orange
855RA	BCI	3 (10)	Redel M-7	855RA	VM3/COP/32.02	White	White	White	White	Or/Br
856RA	Nellcor	0.9 (3)	D-M-9	856RA	VM3/COP/32.03	Blue	Blue	White	White	Blue
857RA	Spacelabs	3 (10)	Hypertronics M-12	857RA	VM3/COP/32.04	White	White	White	White	Orange
858RA	Nellcor	3.65 (12)	D-M-9	858RA	VM3/COP/32.05	Blue	Blue	White	White	Blue
859RA	Pace Tech	3.65 (12)	Switchcraft F-5	859RA	VM3/COP/32.06	White	White	White	White	Orange
860RA	Simed Baxter	3.65 (12)	Hypertronics M-9	860RA	VM3/COP/32.07	White	White	White	White	Orange
861RA	BCI	0.9 (3)	D-M-9	861RA	VM3/COP/32.08	Orange	Orange	White	White	Or/Br
862RA	Criticare	3 (10)	Lemo M-5	862RA	VM3/COP/32.09	Purple	Purple	White	White	Purple
863RA	Datascope	0.9 (3)	D-M-9	863RA	VM3/COP/32.10	Red	Red	White	White	White
864RA	Datascope	3.65 (12)	DIN M-8	864RA	VM3/COP/32.11	Red	Red	White	White	White
865RA	Sensormedics	0.9 (3)	Compu-shield	865RA	VM3/COP/32.12	White	White	White	White	Orange
866RA	Simed Baxter	3.65 (12)	Hypertronics M-9	866RA	VM3/COP/32.13	White	White	White	White	Orange
867RA	Ohmeda	3.65 (12)	Hypertronics M-9	867RA	No diagram details	Green	Green	Black	White	Green
869RA	Criticare	0.9 (3)	D-M-9	869RA	VM3/COP/32.15	Purple	Purple	White	White	Purple
871RA	Nonin	0.9 (3)	D-M-9	871RA	VM3/COP/32.16	White	White	White	White	Orange
872RA	Datex	3.65 (12)	DPK1 F-10	872RA	VM3/COP/32.17	Tan	Tan	White	White	Brown
873RA	Datex	0.9 (3)	D-M-9	873RA	VM3/COP/32.18	Tan	Tan	White	White	Brown
874RA	Palco	0.9 (3)	Sub-min	874RA	VM3/COP/32.19	White	White	White	White	Orange
875RA	Novamatrix	3 (10)	Hypertronics M-7	875RA	VM3/COP/32.20	Yellow	Yellow	Black	White	Yellow
876RA	Novamatrix	3 (10)	Hypertronics M-7	876RA	VM3/COP/32.21	Yellow	Yellow	Black	White	Yellow
877RA	Critikon	0.9 (3)	D-M-9	877RA	VM3/COP/32.22	White	White	White	White	Orange
878RA	In vivo	3 (10)	Lemo M-7	878RA	VM3/COP/32.23	White	White	White	White	Orange
879RA	Artema	3.65 (12)	SPK1-A M-12	879RA	VM3/COP/32.24	White	White	White	White	Orange
885RA	Novamatrix	0.9 (3)	D-M-9	885RA	VM3/COP/32.25	Yellow	Yellow	Black	White	Yellow
886RA	Kontron	3.65 (12)	SPK1-A M-12	886RA	VM3/COP/32.26	White	White	White	White	Orange
887RA	Spacelabs	3 (10)	Hypertronics M-12	887RA	VM3/COP/32.27	White	White	Black	White	Orange
888RA	S&W	3.65 (12)	SPK1-O F-10	888RA	VM3/COP/32.28	White	White	Black	White	Orange
889RA	Criticare	3 (10)	D-M-9	889RA	VM3/COP/32.29	Purple	Purple	White	White	Purple
890RA	Critikon & Sensormedics	3 (10)	Thorkom F-12	890RA	VM3/COP/32.30	White	White	White	White	Orange
891RA	Critikon	3 (10)	Lemo M-7	891RA	VM3/COP/32.31	White	White	White	White	Orange
892RA	Marquette	3 (10)	Marquette M-11	892RA	VM3/COP/32.32	White	White	White	White	Orange
895RA	Hewlett Packard	3 (10)	HP M-12	895RA	No confirmation	White	White	White	White	Orange
896RA	S&W	3.65 (12)	SPK1-N F-10	896RA	VM3/COP/32.34	White	White	White	White	Orange

SpO₂ Finger Probe Details

04 June 2004

Model	Compatible manufacturer	Length M (ft)	Connector type	Model	Document Name VM3/COP/.....
854RA	Medlab/Comdek	3 (10)	Redel M-7	854RA	VM3/COP/32.01
855RA	BCI	3 (10)	Redel M-7	855RA	VM3/COP/32.02
856RA	Nelcor	0.9 (3)	D-M-9	856RA	VM3/COP/32.03
857RA	Spacelabs	3 (10)	Hypertronics M-12	857RA	VM3/COP/32.04
858RA	Nelcor	3.65 (12)	D-M-9	858RA	VM3/COP/32.05
859RA	Pace Tech	3.65 (12)	Switchcraft F-5	859RA	VM3/COP/32.06
860RA	Simed Baxter	3.65 (12)	Hypertronics M-9	860RA	VM3/COP/32.07
861RA	BCI	0.9 (3)	D-M-9	861RA	VM3/COP/32.08
	BCI	Pre made		"	VM3/COP/32.08.1
862RA	Criticare	3 (10)	Lemo M-5	862RA	VM3/COP/32.09
863RA	Datascope	0.9 (3)	D-M-9	863RA	VM3/COP/32.10
864RA	Datascope	3.65 (12)	DIN M-8	864RA	VM3/COP/32.11
865RA	Sensormedics	0.9 (3)	Compu-shield	865RA	VM3/COP/32.12
866RA	Simed Baxter	3.65 (12)	Hypertronics M-9	866RA	VM3/COP/32.13
867RA	Ohmeda	3.65 (12)	Hypertronics M-9	867RA	VM3/COP/32.13
868RA	Criticare	0.9 (3)	D-M-9 (90 degree)	868RA	VM3/COP/32.35
869RA	Criticare	0.9 (3)	D-M-9	869RA	VM3/COP/32.15
870RA	Criticare	3 (10)	D-M-9 (90 degree)	870RA	VM3/COP/32.36
871RA	Nonin	0.9 (3)	D-M-9	871RA	VM3/COP/32.16
	Nonin	Pre made		"	VM3/COP/32.16.1
872RA	Datex	3.65 (12)	DPK1 F-10	872RA	VM3/COP/32.17
873RA	Datex	0.9 (3)	D-M-9	873RA	VM3/COP/32.18
874RA	Palco	0.9 (3)	Sub-min	874RA	VM3/COP/32.19
875RA	Novametrix	3 (10)	Hypertronics M-7	875RA	VM3/COP/32.20
876RA	Novametrix	3 (10)	Hypertronics M-7	876RA	VM3/COP/32.21
877RA	Critikon	0.9 (3)	D-M-9	877RA	VM3/COP/32.22
878RA	Invivo	3 (10)	Lemo M-7	878RA	VM3/COP/32.23
879RA	Artema	3.65 (12)	SPK1-A M-12	879RA	VM3/COP/32.24
885RA	Novametrix	0.9 (3)	D-M-9	885RA	VM3/COP/32.25
886RA	Kontron	3.65 (12)	SPK1-A M-12	886RA	VM3/COP/32.26
887RA	Spacelabs	3 (10)	Hypertronics M-12	887RA	VM3/COP/32.27
888RA	S&W	3.65 (12)	SPK1-O F-10	888RA	VM3/COP/32.28
889RA	Criticare	3 (10)	D-M-9	889RA	VM3/COP/32.29
890RA	Critikon & Sensormedics	3 (10)	Thorkom F-12	890RA	VM3/COP/32.30
891RA	Critikon	3 (10)	Lemo M-7	891RA	VM3/COP/32.31
892RA	Marquette	3 (10)	Marquette M-11	892RA	Not made Yet
895RA	Hewlett Packard	3 (10)	HP M-12	895RA	No confirmation
896RA	S&W	3.65 (12)	SPK1-N F-10	896RA	VM3/COP/32.34
Next Available Document Number				VM3/COP/32.37	