

Measurement Range:	0 % ... 100 % oxygen
Output in Ambient Air:	9 to 13 mV
Electrical Interface:	3 pin (Molex 22-11-1031)
Repeatability:	< 1% vol. O ₂ @ constant temperature and pressure
Linearity error:	0.1 to 1.0 bar ppO ₂ < 3% relative
	0.1 to 2.5 bar ppO ₂ < 5% relative (at ppO ₂ > 1.0 bar after 1 h equilibration time)
Response time:	< 5 sec. to 90% of final value
Zero Offset Voltage:	< 0.5% oxygen reading in 100% nitrogen @ 25°C after 36 seconds
Cross Interference:	< 0.5% vol. O ₂ response to: 5% CO ₂ balance N ₂
Influence of Humidity:	- 0.03% rel. per % RH at 25°C
Pressure Range:	600 to 2500 mbar
Influence of Mechanical Shock:	< 1% relative after a fall from 1m
Operating Temperature:	0°C to 50°C
Temperature Compensation:	Built-in NTC compensation
Effect of Temperature Compensation (steady state):	Between 0°C and +50°C: 5% relative error
Operating Humidity:	0 - 99% RH non-condensing
Long Term Output Drift:	< 1% vol. oxygen per month
	Typically < -15% relative over lifetime
Storage Temperature:	-20°C to +50°C
Recommended Storage:	+5°C to +15°C
Recommended Load:	≥10 kOhms
Warm-Up Time:	< 30 minutes, after replacement of sensor
Nominal Sensor Lifetime:	500,000% vol oxygen hours
Weight:	Approximately 28 grams
Warranty Period:	15 months (including 3-month shelf life)
Part No.:	OOD103: 1001570 (REF 8010000 / VST2200)
	OOD103: 1001570 (REF 8010006 / CR22D)
	OOD103: 1001570 (REF 8010008 / NaNM01)
	OOD103: 1001570 (REF 8010014 / K-22D)
	OOD103: 1001570 (REF 8010015 / UDT-22)
	OOD103: 1001570 (REF 8010018 / M3S)
	OOD103: 1001570 (REF 8010019 / SG-22)
	OOD103: 1001570 (REF 8010020 / 22D)
	OOD103: 1001570 (REF 8010021 / DST-2200)
	OOD103: 1002749 (REF 8010026 / MDS100)

All specifications are applicable at standard conditions: 1013 mbar, 25°C dry ambient air.

Product Specification

Oxygen Sensor


OOD103

Confidential - For Vandagraph only!

ENVITEC

by Honeywell

Mechanical draft:



General tolerances ISO 2768-c

*Intermediate thread: Metric / Unified Extra Fine

Product Specification

Oxygen Sensor

OOD103

Confidential - For Vandagraph only!


ENVITEC

by Honeywell

Customized Design Specification:

- Integration of additional Zitex membrane in sensor gas diffusion way
- Conformal coating on the sensor PCB with PLASTIK 70
- 2 x 2mm holes drilled in the sensor PCB
- No information about EnviteC on PCB top / bottom sides, information for ordering process and traceability only.

PCB Layout:



Product Labeling

OOD103: 1001570 (REF 8010000 / VST2200)	
Label on Sensor (90x15)	Label on Blister- Card (63,5x46,6)
Vandagraph Sensor Technologies 15 Station Road, Cross Hills Keighley, West Yorkshire BD20 7DT, United Kingdom VST2200 Oxygen Sensor S/N A123456 2010-06 	Vandagraph Sensor Technologies e-mail: info@vandagraphst.com 15 Station Road, Cross Hills Keighley, West Yorkshire BD20 7DT, United Kingdom Tel. +44 (0)1535 634900 VST2200 Oxygen Sensor 2010-06 S/N A123456  This oxygen sensor contains caustic liquid, in case of leakage avoid contact with eyes and skin. Do not puncture or staple this bag. Do not remove the oxygen sensor from this bag until ready to use. Depending upon the ambient conditions the oxygen sensor may require 30 minutes to reach signal stability after installation.
OOD103: 1001570 (REF 8010006 / CR22D)	
Label on Sensor (90x15)	Label on Blister- Card (63,5x46,6)
rEvo bvba CR22D - rEvo OXYGEN SENSOR S/N 10612345 Web: www.info@revo-rebreathers.com WARNING: CONTAINS CORROSIVE MATERIAL INSTALL SENSOR PRIOR TO: February 2012 Follow manufacturers recommendations for sensor replacement	rEvo bvba CR22D - rEvo OXYGEN SENSOR SERIAL NO.: 10612345 WARNING ! 1. Sensor contains corrosive electrolyte. 2. Do not puncture or remove sealed membranes. 3. Use eye and hand protection if sensor leaks. 4. Flush and wipe electrolyte from all surfaces. 5. Electrolyte can be harmful or fatal if swallowed. 6. Return sensors damaged in transit to factory. 7. Do not push on either end of sensor. 8. Store at reduced temperature to extend life. INSTALLATION AND REPLACEMENT OF OXYGEN SENSORS: PLEASE REFER TO YOUR MANUFACTURERS MANUAL FOR RECOMMENDATIONS AND INSTALLATION INSTRUCTIONS. INSTALL SENSOR PRIOR TO: February 2012

Product Specification

Oxygen Sensor

OOD103


Confidential - For Vandagraph only!

ENVITEC

by Honeywell

OOD103: 1001570 (REF 8010008 / NaNM01)

Label on Sensor (90x15)




Label on Blister- Card (63,5x46,6)



OOD103: 1001570 (REF 8010014 / K-22D)

Label on Sensor (90x15)



Label on Blister- Card (63,5x46,6)




OOD103: 1001570 (REF 8010015 / UDT-22)

Label on Sensor (90x15)



Label on Blister- Card (63,5x46,6)



OOD103: 1001570 (REF 8010018 / M3S)

Label on Sensor (90x15)



Label on Blister- Card (63,5x46,6)



Product Specification

Oxygen Sensor

OOD103

Confidential - For Vandagraph only!

ENVITEC

by Honeywell

OOD103: 1001570 (REF 8010019 / SG-22)

Label on Sensor (90x15)

 SubGravity
12356 S. 900 E. Suite 103
Draper, UT 84020, USA
www.sub-gravity.com
info@sub-gravity.com

 SG-22 Oxygen Sensor

   2014-07

S/N SG123456



Label on Blister- Card (63,5x46,6)



SubGravity
12356 S. 900 E. Suite 103
Draper, UT 84020, USA
www.sub-gravity.com
+1 801.256.6608
info@sub-gravity.com

SG-22 Oxygen Sensor



2014-07

S/N SG123456



This oxygen sensor contains caustic liquid, in case of leakage avoid contact with eyes and skin. Do not puncture or staple this bag. Do not remove the oxygen sensor from this bag until ready to use. Depending upon the ambient conditions the oxygen sensor may require 30 minutes to reach signal stability after installation.

OOD103: 1001570 (REF 8010020 / 22D)

Label on Sensor (90x15)

DIVESOFT

P/N: 3092
www divesoft.cz
+42 (0) 416 857 057

    2014-07

Oxygen Sensor type 22D

S/N D123456



Label on Blister- Card (63,5x46,6)

DIVESOFT

Háková ulice
413 01 Roudnice nad Labem
Czech Republic
Phone: +42 (0) 416 857 057

P/N: 3092
Website: www divesoft.cz
Email: info@divesoft.cz

Oxygen Sensor type 22D

Fore use with Divesoft Liberty CCR



2014-07

S/N D123456



This oxygen sensor contains caustic liquid, in case of leakage avoid contact with eyes and skin. Do not puncture or staple this bag. Do not remove the oxygen sensor from this bag until ready to use. Depending upon the ambient conditions the oxygen sensor may require 30 minutes to reach signal stability after installation.

OOD103: 1001570 (REF 8010021 / DST-2200)

Label on Sensor (90x15)



Divex3me
www.divex3me.com



2016-01

DST-2200
Oxygen Sensor
S/N D123456



Label on Blister- Card (63,5x46,6)



Divex3me

Via Valvassori Peroni
20133 Milano
Email: contact@divex3me.com
www.divex3me.com

DST-2200 Oxygen Sensor



2016-01

S/N D123456



This oxygen sensor contains caustic liquid, in case of leakage avoid contact with eyes and skin. Do not puncture or staple this bag. Do not remove the oxygen sensor from this bag until ready to use. Depending upon the ambient conditions the oxygen sensor may require 30 minutes to reach signal stability after installation.

OOD103: 1002749 (REF 8010026 / MDS100)

Label on Sensor (90x15)



www.sharkrebreathers.com MDS100 Oxygen Sensor



2019-07

S/N SR1234567



Label on Blister- Card (63,5x46,6)



Email: info@sharkrebreathers.com
www.sharkrebreathers.com

MDS100 Oxygen Sensor



2019-07

S/N SR1234567



This oxygen sensor contains caustic liquid, in case of leakage avoid contact with eyes and skin. Do not puncture or staple this bag. Do not remove the oxygen sensor from this bag until ready to use. Depending upon the ambient conditions the oxygen sensor may require 30 minutes to reach signal stability after installation.

Product Specification

Oxygen Sensor

OOD103

Confidential - For Vandagraph only!

ENVITEC

by Honeywell

Customer Approval

Date: 2nd July 2019

Signature:

