



2305 South 1070 West
West Valley, UT 84119

DOCUMENT NUMBER: R125P04-001-LCS

DOCUMENT TITLE: Label File,Max-250A Ext Phone Jack Sensor

DOCUMENT NOTES:

Document Information

Revision: R	Vault: Regulatory-rel
Doc Type: Labeling	Status: Release

Date Information

Effective Date: 11 Sep 2024	Next Review Date: 11 Sep 2026
Release Date: 11 Sep 2024	Expiration Date:

Control Information

Author: Regulatory Creator/Reviser	Previous Number:
Owner: Regulatory Creator/Reviser	Change Number: DC-0123-24

All dates and times are in US/Mountain

LABEL CONTROL SHEET

Revision # RMAXTEC PART NUMBER: R125P04-001DESCRIPTION: MAX-250A EXTERNAL PHONE JACK OXYGEN SENSORNum. of Labels: 3

GTIN NUMBER SHOULD READ: 00853061006524

LABEL STOCK NUM: RP35P17-006
 LABEL DESCRIPTION: 2.875 X 1.25 Sensor Label Stock
 FILE PATH: Z:\LABEL FILE\ MAX-250 R125P04-001

TO PRINT LABEL CHANGE SERIAL NUMBER TO YMJJJXXSSS FORMAT, CHANGE MANUFACTURING DATE USING TODAY'S DATE AND YYYY-MM-DD SEQUENCE, CHANGE THE MANUFACTURING DATE IN THE BARCODE BY GOING INTO DATA SOURCE PROPERTIES AND CHANGING THE DIGITS AFTER THE(11) AND BEFORE THE (21) TO TODAYS DATE USING YYMMDD FORMAT AND USE THERMAL TRANSFER RIBBON



LABEL STOCK NUM: RP35P10-002
 LABEL DESCRIPTION: 1.75 x 3.5 WHITE CARDSTOCK LABEL STOCK
 FILE PATH: Z:\LABEL FILE\ MAX-250 R125P04-001 CARDSTOCK

TO PRINT LABEL CHANGE SERIAL NUMBER TO YMJJJXXSSS FORMAT, CHANGE MANUFACTURING DATE USING TODAY'S DATE AND YYYY-MM-DD SEQUENCE, CHANGE THE MANUFACTURING DATE IN THE BARCODE BY GOING INTO DATA SOURCE PROPERTIES AND CHANGING THE DIGITS AFTER THE(11) AND BEFORE THE (21) TO TODAYS DATE USING YYMMDD FORMAT AND USE THERMAL TRANSFER RIBBON

OXYGEN SENSOR		SN	*KC99099000*
REF	R125P04-001 MAX-250A		
Handle with care - Dropping can adversely affect performance.			
Optimal Storage Temperature Range: 5 to 25 °C Maximum Storage Temperature Range: -15 to 50 °C For optimal sensor life install within 12 months from date of manufacture		EC	REP
Visit www.maxtec.com for further information Remove Protective Tab at time of use MADE IN THE USA			EMERGO EUROPE Westervoortsedijk 60, 6827 AT Arnhem The Netherlands
UDI		Rx ONLY	CE 0123
(01)00853061006524(11)240415(21)KC99099000			
		TP-0057 (01)	

MAXTEC

OPERATIONAL PROCEDURE

IN-HOUSE LABEL TO BE PULLED AT KITTING: R137P11

UK	REP	Emergo Consulting (UK) Limited c/o Cr 360 - UL International, Compass House, Vision Park Histon, Cambridge CB24 9BZ, United Kingdom
TP-0148 Rev 02		

Released

FRM-0137 Rev. 01

2 of 2

Signature Manifest**Document Number:** R125P04-001-LCS**Revision:** R**Title:** Label File,Max-250A Ext Phone Jack Sensor**Effective Date:** 11 Sep 2024

All dates and times are in US/Mountain.

DC-0123-24 Max- Sensor Label Stock Update**Doc Control Review**

Name/Signature	Title	Date	Meaning/Reason
Diana Larsen (DLARSEN)	Document Control Specialist	06 Sep 2024, 01:25:26 PM	Complete

Management Approval

Name/Signature	Title	Date	Meaning/Reason
Anvitha AnandRao (ANVITHA)	Regulatory & Quality Product Engineering Specialist.	09 Sep 2024, 09:54:12 AM	Approved
Doree Wallo (DWALLO)	Quality Manager	09 Sep 2024, 11:57:54 AM	Approved
Matthew Swank (MSWANK)	Chief Engineer	09 Sep 2024, 03:20:03 PM	Approved
Sri Kadiyala (SKADIYALA)	Regulatory and Quality Systems Specialist	09 Sep 2024, 04:00:57 PM	Approved
Brian Fischer (BFISCHER)	Engineer	10 Sep 2024, 08:49:43 AM	Approved
Shawn Smith (SSMITH)	Chief Operating Officer	11 Sep 2024, 10:18:37 AM	Approved

Quality Approval

Name/Signature	Title	Date	Meaning/Reason
Diana Larsen (DLARSEN)	Document Control Specialist	11 Sep 2024, 11:53:29 AM	Approved

Training/Disposition

Name/Signature	Title	Date	Meaning/Reason
Diana Larsen (DLARSEN)	Document Control Specialist	11 Sep 2024, 11:54:13 AM	Approved